

INDUSTRIAL BP, BPHE, & BN SERIES FILTER BAGS



Industrial[§] BP, BPHE & BN Series Filter Bags feature a thermally-welded, unique design that results in consistent filtration efficiencies. They are designed to fit the BPHE-410 and BPHE-420 Housings. Higher productivity can be achieved with faster bag change-outs. The semi-rigid cylindrical design is easily crushed and incinerated.

FEATURES/BENEFITS

BP Series (Polypropylene Felt)

Filtration ratings from 1 to 200 microns nominal to comply with any filtration requirement

Manufactured from felt due to its high solids loading capabilities versus similar mesh fabrics

A glazed finish, created by melting the outermost surface fibers, is used to produce a bond that reduces the possibility of migration

BPHE Series (High-Efficiency)

For those critical applications when high-efficiency combined with high dirt-holding capacity is required

Polypropylene materials are processed into microfibers with diameters of 1 to 10 microns or more, then converted into filter material

Microfiber media is covered with spunbonded polypropylene

BN Series (Strainer)

Woven monofilment materials are offered in nylon with nominal micron ratings of 50 to 800

Efficiencies from 75 to 95%

Materials are cleanable and reusable

APPLICATIONS

Acids Alkalis Corrosive Fluids Micro-organisms Oils Organic Solvents

BAG SPECIFICATIONS & PERFORMANCE

MODEL	DIMENSIONS	FILTER MEDIA	μ (NOMINAL)	CASE QTY.	MAX. TEMP.
BP-410	4" x 8.625" (102 mm x 218 mm)	Glazed polypropylene felt	1, 5, 10, 25, 50, 100, 200	20	
BP-420	4" x 18" (102 mm x 457 mm)	Glazed polypropylene felt	1, 5, 10, 25, 50, 100, 200	20	
BPHE-410	4" x 8.625" (102 mm x 218 mm)	Polypropylene microfibers with spun-bonded polypropylene covers	1, 5, 10, 25, 50, 75, 100	20	200°F
BPHE-420	4" x 18" (102 mm x 457 mm)	Polypropylene microfibers with spun-bonded polypropylene covers	1, 5, 10, 25, 50, 75, 100	20	(93.3°C)
BN-410	4" x 8.625" (102 mm x 218 mm)	Nylon monofilament mesh	50, 100, 150, 200, 250, 300, 400, 600, 800	20	
BN-420	4" x 18" (102 mm x 457 mm)	Nylon monofilament mesh	50, 100, 150, 200, 250, 300, 400, 600, 800	20	

PRESSURE DROP VS FLOW RATE

Polypropylene Felt Bags



GPM, 1 cps @77°F (Lpm, 1 cps @ 25°C)

High Efficiency Bags



The following chart is based on 1 centipoise. (CPS)

If your liquid is greater than 1 CPS:

- 1. Select your liquid's viscosity
- 2. Determine your correction factor

EX: If your liquid's viscosity is 100, your correction factor is 8.3

3. Multiply the Bag Selection Guide (left) by your correction factor.

factor

VISCOSITY (CPS)	CORRECTION FACTOR
50	4.5
100	8.3
200	16.6
400	27.7
800	50.0
1,000	56.2
1,500	77.2
2,000	113.6
4,000	161.0
6,000	250.0
8,000	325.0
10,000	430.0

WARNING: For drinking water applications, do not use with water that is microbiologically unsafe or of unknown quality without adequate disinfection before or after the system.

NOTE: This information is for general guidance. Users should test bag materials with media involved to determine compatibility.

CAUTION: Protect against freezing to prevent cracking of the filter and water leakage.



WATER QUALITY SYSTEMS 5730 NORTH GLEN PARK ROAD, MILWAUKEE, WI 53209 P: 262.238.4400 | F: 262.238.4404 PENTAIRINDUSTRIAL.COM CUSTOMER CARE: 800.279.9404 | tech-support@pentair.com $\ensuremath{\mathbb{C}}$ 2015 Pentair Residential Filtration, LLC. All rights reserved.

[§]For a detailed list of where Pentair trademarks are registered, please visit waterpurification.pentair.com. Pentair trademarks and logos are owned by Pentair LLC or its affiliates. Third party registered and unregistered trademarks and logos are the property of their respective owners. 4003015 Rev E NV15